

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752302

Luminaire Tested: LD4D70BD010-EU4DR3570959027-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752302
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5897.2 lumens
Efficiency: N/A
Efficacy: 88.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752302

CATALOG NUMBER: LD4D70BD010-EU4DR3570959027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752302

CATALOG NUMBER: LD4D70BD010-EU4DR3570959027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1772865
5°	1731214
10°	1560282
15°	1211021
20°	686882
25°	267224
30°	99694
35°	54647
40°	35714
45°	21741
50°	13836
55°	9772
60°	7146
65°	3878
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21741 cd/sqm

TEST NUMBER: P752302

CATALOG NUMBER: LD4D70BD010-EU4DR3570959027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1451.7	24.6
10°-20°	2834.4	48.1
20°-30°	1156.0	19.6
30°-40°	276.6	4.7
40°-50°	115.3	2.0
50°-60°	47.7	0.8
60°-70°	14.9	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5442.0	92.3
0°-40°	5718.7	97.0
0°-60°	5881.6	99.7
0°-90°	5897.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5897.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16226	
5°	15784	###
15°	10706	2834
25°	2217	1156
35°	410	277
45°	141	115
55°	51	48
65°	15	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752302

CATALOG NUMBER: LD4D70BD010-EU4DR3570959027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	16226.0
2.5°	16128.7
5°	15784.5
7.5°	15097.8
10°	14063.4
12.5°	12606.9
15°	10706.1
17.5°	8381.6
20°	5907.5
22.5°	3766.9
25°	2216.6
27.5°	1253.0
30°	790.2
32.5°	554.8
35°	409.7
37.5°	316.8
40°	250.4
42.5°	192.9
45°	140.7
47.5°	105.3
50°	81.4
52.5°	64.6
55°	51.3
57.5°	41.6
60°	32.7
62.5°	23.9
65°	15.0
67.5°	5.3
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)