

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752339

Luminaire Tested: LD4D70BD010-EU4DR3570959040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6853.1 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752339

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBDP1H

Luminous Intensity Polar Plot



TEST NUMBER: P752339

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2060254
5°	2011848
10°	1813206
15°	1407344
20°	798225
25°	310540
30°	115856
35°	63504
40°	41505
45°	25264
50°	16080
55°	11353
60°	8304
65°	4524
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25264 cd/sqm



TEST NUMBER: P752339

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1687.0	24.6
10°-20°	3293.8	48.1
20°-30°	1343.3	19.6
30°-40°	321.5	4.7
40°-50°	134.0	2.0
50°-60°	55.4	0.8
60°-70°	17.4	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6324.2	92.3
0°-40°	6645.7	97.0
0°-60°	6835.1	99.7
0°-90°	6853.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6853.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	18856	
5°	18343	###
15°	12442	3294
25°	2576	1343
35°	476	321
45°	164	134
55°	60	55
65°	18	17
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752339

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	18856.3
2.5°	18743.2
5°	18343.2
7.5°	17545.2
10°	16343.1
12.5°	14650.5
15°	12441.7
17.5°	9740.3
20°	6865.1
22.5°	4377.6
25°	2575.9
27.5°	1456.1
30°	918.3
32.5°	644.8
35°	476.1
37.5°	368.1
40°	291.0
42.5°	224.2
45°	163.5
47.5°	122.4
50°	94.6
52.5°	75.1
55°	59.6
57.5°	48.3
60°	38.0
62.5°	27.8
65°	17.5
67.5°	6.2
70°	1.0
72.5°	1.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)