

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752693

Luminaire Tested: LD4D70BD010-EU4DR6070959027-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6512.7 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752693

CATALOG NUMBER: LD4D70BD010-EU4DR6070959027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P752693

CATALOG NUMBER: LD4D70BD010-EU4DR6070959027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	712107
5°	710363
10°	733965
15°	734716
20°	676022
25°	575003
30°	438128
35°	309821
40°	181939
45°	73412
50°	24511
55°	11791
60°	4851
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 73412 cd/sqm

TEST NUMBER: P752693

CATALOG NUMBER: LD4D70BD010-EU4DR6070959027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	624.8	9.6
10°-20°	1799.4	27.6
20°-30°	2153.7	33.1
30°-40°	1440.5	22.1
40°-50°	427.1	6.6
50°-60°	61.4	0.9
60°-70°	5.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4577.9	70.3
0°-40°	6018.4	92.4
0°-60°	6506.8	99.9
0°-90°	6512.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6512.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6518	
5°	6477	625
15°	6495	1799
25°	4770	2154
35°	2323	1440
45°	475	427
55°	62	61
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752693

CATALOG NUMBER: LD4D70BD010-EU4DR6070959027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	6517.5
2.5°	6509.2
5°	6476.8
7.5°	6564.6
10°	6615.5
12.5°	6606.2
15°	6495.3
17.5°	6233.7
20°	5814.1
22.5°	5310.3
25°	4769.6
27.5°	4160.4
30°	3472.7
32.5°	2859.0
35°	2322.8
37.5°	1785.8
40°	1275.6
42.5°	841.1
45°	475.1
47.5°	243.1
50°	144.2
52.5°	93.4
55°	61.9
57.5°	39.7
60°	22.2
62.5°	9.2
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)