

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752416

Luminaire Tested: LD4D70BD010-EU4DR4070959040-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752416
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4070959040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6675.2 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752416

CATALOG NUMBER: LD4D70BD010-EU4DR4070959040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P752416

CATALOG NUMBER: LD4D70BD010-EU4DR4070959040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1698076
5°	1689833
10°	1597260
15°	1357867
20°	925486
25°	386153
30°	121420
35°	56434
40°	31207
45°	14308
50°	6952
55°	3810
60°	1989
65°	698
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14308 cd/sqm



TEST NUMBER: P752416

CATALOG NUMBER: LD4D70BD010-EU4DR4070959040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1438.6	21.6
10°-20°	3222.9	48.3
20°-30°	1613.3	24.2
30°-40°	295.7	4.4
40°-50°	81.6	1.2
50°-60°	19.2	0.3
60°-70°	3.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6274.9	94.0
0°-40°	6570.6	98.4
0°-60°	6671.4	99.9
0°-90°	6675.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6675.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15542	
5°	15407	###
15°	12004	3223
25°	3203	1613
35°	423	296
45°	93	82
55°	20	19
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752416

CATALOG NUMBER: LD4D70BD010-EU4DR4070959040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	15541.5
2.5°	15518.8
5°	15407.2
7.5°	15051.3
10°	14396.7
12.5°	13376.2
15°	12004.3
17.5°	10220.3
20°	7959.6
22.5°	5426.6
25°	3203.1
27.5°	1693.2
30°	962.4
32.5°	621.9
35°	423.1
37.5°	302.3
40°	218.8
42.5°	149.8
45°	92.6
47.5°	59.0
50°	40.9
52.5°	29.1
55°	20.0
57.5°	12.7
60°	9.1
62.5°	5.4
65°	2.7
67.5°	1.8
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)