

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752772

Luminaire Tested: LD4D70BD010-EU4DR6570959027-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P752772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6570959027-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6072.8 lumens
Efficiency: N/A
Efficacy: 91.2 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752772

CATALOG NUMBER: LD4D70BD010-EU4DR6570959027-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P752772

CATALOG NUMBER: LD4D70BD010-EU4DR6570959027-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	64	59	79	69	63	59	68	63	59		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	61	55	51	71	61	55	51	60	54	51		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	322039
5°	321223
10°	320952
15°	311058
20°	283177
25°	246772
30°	205244
35°	162624
40°	117373
45°	74154
50°	38652
55°	20548
60°	10793
65°	5929
70°	2493
75°	2753
80°	1917
85°	1608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 74154 cd/sqm



TEST NUMBER: P752772

CATALOG NUMBER: LD4D70BD010-EU4DR6570959027-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	521.4	8.6
10°-20°	1427.9	23.5
20°-30°	1745.4	28.7
30°-40°	1416.2	23.3
40°-50°	705.7	11.6
50°-60°	196.8	3.2
60°-70°	44.7	0.7
70°-80°	11.7	0.2
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3694.8	60.8
0°-40°	5110.9	84.2
0°-60°	6013.5	99.0
0°-90°	6072.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6072.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5514	
5°	5479	521
15°	5144	1428
25°	3829	1745
35°	2281	1416
45°	898	706
55°	202	197
65°	43	45
75°	12	12
85°	2	3
90°	0	



TEST NUMBER: P752772

CATALOG NUMBER: LD4D70BD010-EU4DR6570959027-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	5514.0
2.5°	5509.9
5°	5479.1
7.5°	5461.3
10°	5411.9
12.5°	5311.4
15°	5144.5
17.5°	4883.6
20°	4556.2
22.5°	4202.9
25°	3829.4
27.5°	3429.9
30°	3043.4
32.5°	2661.8
35°	2280.9
37.5°	1900.9
40°	1539.5
42.5°	1200.8
45°	897.8
47.5°	625.5
50°	425.4
52.5°	293.3
55°	201.8
57.5°	136.1
60°	92.4
62.5°	64.0
65°	42.9
67.5°	21.9
70°	14.6
72.5°	13.8
75°	12.2
77.5°	8.1
80°	5.7
82.5°	4.1
85°	2.4
87.5°	1.6
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)