

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752734

Luminaire Tested: LD4D70BD010-EU4DR6070959040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752734
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7952.6 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752734

CATALOG NUMBER: LD4D70BD010-EU4DR6070959040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752734

CATALOG NUMBER: LD4D70BD010-EU4DR6070959040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	869541
5°	867422
10°	896235
15°	897161
20°	825479
25°	702130
30°	534996
35°	378327
40°	222160
45°	89651
50°	29933
55°	14401
60°	5922
65°	879
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 89651 cd/sqm



TEST NUMBER: P752734

CATALOG NUMBER: LD4D70BD010-EU4DR6070959040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	762.9	9.6
10°-20°	2197.3	27.6
20°-30°	2629.9	33.1
30°-40°	1758.9	22.1
40°-50°	521.5	6.6
50°-60°	75.0	0.9
60°-70°	7.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5590.0	70.3
0°-40°	7349.0	92.4
0°-60°	7945.5	99.9
0°-90°	7952.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7952.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7958	
5°	7909	763
15°	7931	2197
25°	5824	2630
35°	2836	1759
45°	580	522
55°	76	75
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752734

CATALOG NUMBER: LD4D70BD010-EU4DR6070959040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7958.4
2.5°	7948.3
5°	7908.8
7.5°	8016.0
10°	8078.1
12.5°	8066.8
15°	7931.4
17.5°	7611.9
20°	7099.5
22.5°	6484.4
25°	5824.1
27.5°	5080.3
30°	4240.5
32.5°	3491.1
35°	2836.4
37.5°	2180.6
40°	1557.6
42.5°	1027.1
45°	580.2
47.5°	296.8
50°	176.1
52.5°	114.0
55°	75.6
57.5°	48.5
60°	27.1
62.5°	11.3
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)