

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752318

Luminaire Tested: LD4D70BD010-EU4DR3570959030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752318
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7160.8 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752318

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P752318

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2152743
5°	2102157
10°	1894607
15°	1470518
20°	834060
25°	324488
30°	121054
35°	66358
40°	43374
45°	26392
50°	16811
55°	11868
60°	8697
65°	4731
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26392 cd/sqm



TEST NUMBER: P752318

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1762.8	24.6
10°-20°	3441.7	48.1
20°-30°	1403.7	19.6
30°-40°	335.9	4.7
40°-50°	140.0	2.0
50°-60°	57.9	0.8
60°-70°	18.1	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6608.1	92.3
0°-40°	6944.0	97.0
0°-60°	7141.9	99.7
0°-90°	7160.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7160.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19703	
5°	19167	###
15°	13000	3442
25°	2692	1404
35°	498	336
45°	171	140
55°	62	58
65°	18	18
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752318

CATALOG NUMBER: LD4D70BD010-EU4DR3570959030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	19702.8
2.5°	19584.6
5°	19166.6
7.5°	18332.8
10°	17076.8
12.5°	15308.2
15°	13000.2
17.5°	10177.5
20°	7173.3
22.5°	4574.1
25°	2691.6
27.5°	1521.5
30°	959.5
32.5°	673.7
35°	497.5
37.5°	384.7
40°	304.1
42.5°	234.2
45°	170.8
47.5°	127.9
50°	98.9
52.5°	78.4
55°	62.3
57.5°	50.5
60°	39.8
62.5°	29.0
65°	18.3
67.5°	6.4
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)