

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752474

Luminaire Tested: LD4D70BD010-EU4DR4570959030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752474
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4570959030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7678.4 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752474

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752474

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		98	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	91		103	98	94	91		95	92	89		93	90	88		91	89	87
4	100	94	89	85		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	83	80		86	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	75	72		87	80	75	72		79	74	71		78	74	71		77	73	71
8	85	77	72	68		84	76	71	68		75	71	68		74	70	67		73	70	67
9	82	73	68	65		81	73	68	65		72	68	65		71	67	64		71	67	64
10	79	70	65	62		78	70	65	62		69	65	62		68	64	61		68	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1482865
5°	1440644
10°	1378308
15°	1261436
20°	1000761
25°	624793
30°	344363
35°	154631
40°	60903
45°	28694
50°	13615
55°	7124
60°	3496
65°	827
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28694 cd/sqm



TEST NUMBER: P752474

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1234.2	16.1
10°-20°	3037.5	39.6
20°-30°	2405.4	31.3
30°-40°	801.0	10.4
40°-50°	159.0	2.1
50°-60°	36.1	0.5
60°-70°	5.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6677.0	87.0
0°-40°	7478.0	97.4
0°-60°	7673.1	99.9
0°-90°	7678.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7678.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13572	
5°	13135	###
15°	11152	3037
25°	5183	2405
35°	1159	801
45°	186	159
55°	37	36
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752474

CATALOG NUMBER: LD4D70BD010-EU4DR4570959030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13571.8
2.5°	13483.2
5°	13135.2
7.5°	12848.0
10°	12423.2
12.5°	11857.4
15°	11151.8
17.5°	10090.8
20°	8607.0
22.5°	6839.3
25°	5182.6
27.5°	3794.8
30°	2729.5
32.5°	1856.3
35°	1159.3
37.5°	687.4
40°	427.0
42.5°	280.7
45°	185.7
47.5°	119.6
50°	80.1
52.5°	53.4
55°	37.4
57.5°	24.6
60°	16.0
62.5°	8.5
65°	3.2
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)