

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752546

Luminaire Tested: LD4D70BD010-EU4DR5070959030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752546
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5070959030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6274.4 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752546

CATALOG NUMBER: LD4D70BD010-EU4DR5070959030-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P752546

CATALOG NUMBER: LD4D70BD010-EU4DR5070959030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1104583
5°	1093008
10°	1075003
15°	978875
20°	814538
25°	578198
30°	306047
35°	124713
40°	46312
45°	21200
50°	8686
55°	4553
60°	2229
65°	672
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21200 cd/sqm



TEST NUMBER: P752546

CATALOG NUMBER: LD4D70BD010-EU4DR5070959030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	941.9	15.0
10°-20°	2380.5	37.9
20°-30°	2138.3	34.1
30°-40°	669.5	10.7
40°-50°	117.2	1.9
50°-60°	23.4	0.4
60°-70°	3.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5460.8	87.0
0°-40°	6130.3	97.7
0°-60°	6270.8	99.9
0°-90°	6274.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6274.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10110	
5°	9966	942
15°	8654	2380
25°	4796	2138
35°	935	670
45°	137	117
55°	24	23
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752546

CATALOG NUMBER: LD4D70BD010-EU4DR5070959030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	10109.6
2.5°	10059.3
5°	9965.6
7.5°	9822.4
10°	9689.4
12.5°	9263.2
15°	8653.8
17.5°	7879.9
20°	7005.4
22.5°	5993.7
25°	4796.1
27.5°	3526.1
30°	2425.8
32.5°	1579.4
35°	935.0
37.5°	537.0
40°	324.7
42.5°	211.4
45°	137.2
47.5°	83.5
50°	51.1
52.5°	34.9
55°	23.9
57.5°	16.2
60°	10.2
62.5°	6.0
65°	2.6
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)