

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752625

Luminaire Tested: LD4D70BD010-EU4DR5570959030-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6936.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752625

CATALOG NUMBER: LD4D70BD010-EU4DR5570959030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P752625

CATALOG NUMBER: LD4D70BD010-EU4DR5570959030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	849786
5°	816038
10°	812959
15°	789611
20°	707997
25°	585118
30°	441988
35°	320479
40°	205087
45°	93669
50°	30630
55°	13220
60°	5682
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 93669 cd/sqm



TEST NUMBER: P752625

CATALOG NUMBER: LD4D70BD010-EU4DR5570959030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	708.0	10.2
10°-20°	1932.2	27.9
20°-30°	2201.9	31.7
30°-40°	1499.0	21.6
40°-50°	516.5	7.4
50°-60°	71.4	1.0
60°-70°	6.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4842.1	69.8
0°-40°	6341.1	91.4
0°-60°	6929.1	99.9
0°-90°	6936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6936.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7778	
5°	7440	708
15°	6981	1932
25°	4854	2202
35°	2403	1499
45°	606	517
55°	69	71
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752625

CATALOG NUMBER: LD4D70BD010-EU4DR5570959030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7777.6
2.5°	7599.3
5°	7440.3
7.5°	7362.2
10°	7327.5
12.5°	7211.9
15°	6980.6
17.5°	6613.4
20°	6089.1
22.5°	5483.9
25°	4853.5
27.5°	4197.2
30°	3503.3
32.5°	2915.4
35°	2402.7
37.5°	1915.0
40°	1437.9
42.5°	996.5
45°	606.2
47.5°	326.7
50°	180.2
52.5°	107.0
55°	69.4
57.5°	44.3
60°	26.0
62.5°	11.6
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)