

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752514

Luminaire Tested: LD4D70BD010-EU4DR4570959050-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4570959050-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7397.3 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752514

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752514

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1428584
5°	1387911
10°	1327861
15°	1215263
20°	964123
25°	601924
30°	331759
35°	148962
40°	58678
45°	27643
50°	13105
55°	6858
60°	3365
65°	801
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27643 cd/sqm



TEST NUMBER: P752514

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1189.0	16.1
10°-20°	2926.3	39.6
20°-30°	2317.3	31.3
30°-40°	771.7	10.4
40°-50°	153.2	2.1
50°-60°	34.8	0.5
60°-70°	5.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6432.6	87.0
0°-40°	7204.3	97.4
0°-60°	7392.2	99.9
0°-90°	7397.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7397.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13075	
5°	12654	###
15°	10744	2926
25°	4993	2317
35°	1117	772
45°	179	153
55°	36	35
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752514

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	13075.0
2.5°	12989.6
5°	12654.4
7.5°	12377.8
10°	11968.5
12.5°	11423.4
15°	10743.6
17.5°	9721.4
20°	8291.9
22.5°	6588.9
25°	4992.9
27.5°	3655.9
30°	2629.6
32.5°	1788.4
35°	1116.8
37.5°	662.3
40°	411.4
42.5°	270.5
45°	178.9
47.5°	115.2
50°	77.1
52.5°	51.4
55°	36.0
57.5°	23.7
60°	15.4
62.5°	8.2
65°	3.1
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)