

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752589

Luminaire Tested: LD4D70BD010-EU4DR5070959050-4LBS1B

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P752589  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D70BD010-EU4DR5070959050-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 50° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7466.3 lumens  
Efficiency: N/A  
Efficacy: 112.1 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 66.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P752589

CATALOG NUMBER: LD4D70BD010-EU4DR5070959050-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P752589

CATALOG NUMBER: LD4D70BD010-EU4DR5070959050-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 |  | 106 | 104 | 102 |  |  | 102 | 101 | 99  |  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  |  | 100 | 98  | 95  |  |  | 97  | 95  | 93  |  |  | 95  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  |  | 93  | 90  | 88  |  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  |  | 90  | 87  | 84  |  |  | 89  | 85  | 83  |  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 79  |  | 86  | 82  | 79  |  |  | 85  | 81  | 78  |  |  | 83  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 79  | 75  |  | 82  | 78  | 74  |  |  | 81  | 77  | 74  |  |  | 79  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  |  | 77  | 73  | 70  |  |  | 76  |
| 8   | 85  | 76  | 71  | 67  | 84  | 76  | 71  | 67  |  | 75  | 70  | 67  |  |  | 74  | 70  | 67  |  |  | 73  |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 67  | 64  |  | 71  | 67  | 64  |  |  | 71  | 67  | 64  |  |  | 70  |
| 10  | 78  | 70  | 64  | 61  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  |  | 68  | 64  | 61  |  |  | 67  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1314418 |
| 5°  | 1300640 |
| 10° | 1279222 |
| 15° | 1164836 |
| 20° | 969274  |
| 25° | 688037  |
| 30° | 364183  |
| 35° | 148402  |
| 40° | 55112   |
| 45° | 25233   |
| 50° | 10352   |
| 55° | 5410    |
| 60° | 2666    |
| 65° | 776     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25233 cd/sqm



TEST NUMBER: P752589

CATALOG NUMBER: LD4D70BD010-EU4DR5070959050-4LBS1B

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1120.9 | 15.0      |
| 10°-20°   | 2832.7 | 37.9      |
| 20°-30°   | 2544.5 | 34.1      |
| 30°-40°   | 796.7  | 10.7      |
| 40°-50°   | 139.5  | 1.9       |
| 50°-60°   | 27.8   | 0.4       |
| 60°-70°   | 4.2    | 0.1       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 6498.1 | 87.0      |
| 0°-40°    | 7294.8 | 97.7      |
| 0°-60°    | 7462.1 | 99.9      |
| 0°-90°    | 7466.3 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 7466.3 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°    | Flux |
|-----|-------|------|
| 0°  | 12030 |      |
| 5°  | 11859 | ###  |
| 15° | 10298 | 2833 |
| 25° | 5707  | 2545 |
| 35° | 1113  | 797  |
| 45° | 163   | 139  |
| 55° | 28    | 28   |
| 65° | 3     | 4    |
| 75° | 0     | 0    |
| 85° | 0     | 0    |
| 90° | 0     |      |



TEST NUMBER: P752589

CATALOG NUMBER: LD4D70BD010-EU4DR5070959050-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

|       | 0°      |
|-------|---------|
| 0°    | 12030.1 |
| 2.5°  | 11970.3 |
| 5°    | 11858.7 |
| 7.5°  | 11688.3 |
| 10°   | 11530.1 |
| 12.5° | 11023.0 |
| 15°   | 10297.8 |
| 17.5° | 9376.8  |
| 20°   | 8336.2  |
| 22.5° | 7132.3  |
| 25°   | 5707.2  |
| 27.5° | 4196.0  |
| 30°   | 2886.6  |
| 32.5° | 1879.4  |
| 35°   | 1112.6  |
| 37.5° | 639.0   |
| 40°   | 386.4   |
| 42.5° | 251.5   |
| 45°   | 163.3   |
| 47.5° | 99.4    |
| 50°   | 60.9    |
| 52.5° | 41.6    |
| 55°   | 28.4    |
| 57.5° | 19.3    |
| 60°   | 12.2    |
| 62.5° | 7.1     |
| 65°   | 3.0     |
| 67.5° | 1.0     |
| 70°   | 0.0     |
| 72.5° | 0.0     |
| 75°   | 0.0     |
| 77.5° | 0.0     |
| 80°   | 0.0     |
| 82.5° | 0.0     |
| 85°   | 0.0     |
| 87.5° | 0.0     |
| 90°   | 0.0     |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report





— 0°-180°







(END OF REPORT)