

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752707

Luminaire Tested: LD4D70BD010-EU4DR6070959030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7160.2 lumens
Efficiency: N/A
Efficacy: 107.5 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752707

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBS1H

Luminous Intensity Polar Plot



TEST NUMBER: P752707

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	782908
5°	780985
10°	806934
15°	807766
20°	743228
25°	632171
30°	481692
35°	340633
40°	200024
45°	80705
50°	26942
55°	12972
60°	5332
65°	776
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 80705 cd/sqm



TEST NUMBER: P752707

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	686.9	9.6
10°-20°	1978.3	27.6
20°-30°	2367.8	33.1
30°-40°	1583.7	22.1
40°-50°	469.5	6.6
50°-60°	67.5	0.9
60°-70°	6.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5033.0	70.3
0°-40°	6616.7	92.4
0°-60°	7153.8	99.9
0°-90°	7160.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7160.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7166	
5°	7121	687
15°	7141	1978
25°	5244	2368
35°	2554	1584
45°	522	470
55°	68	68
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752707

CATALOG NUMBER: LD4D70BD010-EU4DR6070959030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7165.5
2.5°	7156.3
5°	7120.7
7.5°	7217.3
10°	7273.2
12.5°	7263.0
15°	7141.1
17.5°	6853.5
20°	6392.1
22.5°	5838.3
25°	5243.8
27.5°	4574.1
30°	3818.0
32.5°	3143.2
35°	2553.8
37.5°	1963.4
40°	1402.4
42.5°	924.8
45°	522.3
47.5°	267.3
50°	158.5
52.5°	102.6
55°	68.1
57.5°	43.7
60°	24.4
62.5°	10.2
65°	3.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)