

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752901

Luminaire Tested: LD4D70BD010-EU4DR7070959050-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752901
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR7070959050-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7146.9 lumens
Efficiency: N/A
Efficacy: 107.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752901

CATALOG NUMBER: LD4D70BD010-EU4DR7070959050-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P752901

CATALOG NUMBER: LD4D70BD010-EU4DR7070959050-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	616329
5°	614790
10°	613455
15°	613287
20°	607293
25°	570471
30°	508577
35°	405497
40°	269242
45°	160977
50°	83460
55°	43870
60°	15515
65°	259
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 160977 cd/sqm



TEST NUMBER: P752901

CATALOG NUMBER: LD4D70BD010-EU4DR7070959050-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	533.1	7.5
10°-20°	1528.9	21.4
20°-30°	2156.8	30.2
30°-40°	1861.9	26.1
40°-50°	833.8	11.7
50°-60°	218.3	3.1
60°-70°	14.2	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4218.7	59.0
0°-40°	6080.6	85.1
0°-60°	7132.7	99.8
0°-90°	7146.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7146.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5641	
5°	5605	533
15°	5422	1529
25°	4732	2157
35°	3040	1862
45°	1042	834
55°	230	218
65°	1	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752901

CATALOG NUMBER: LD4D70BD010-EU4DR7070959050-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5640.9
2.5°	5634.8
5°	5605.4
7.5°	5581.0
10°	5529.3
12.5°	5482.7
15°	5421.8
17.5°	5351.8
20°	5223.0
22.5°	5011.0
25°	4732.0
27.5°	4408.4
30°	4031.1
32.5°	3569.6
35°	3040.1
37.5°	2455.8
40°	1887.7
42.5°	1434.3
45°	1041.8
47.5°	718.2
50°	491.0
52.5°	338.8
55°	230.3
57.5°	139.0
60°	71.0
62.5°	22.3
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)