

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752325

Luminaire Tested: LD4D70BD010-EU4DR3570959035-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752325
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5667.0 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752325

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P752325

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1703659
5°	1663631
10°	1499372
15°	1163750
20°	660058
25°	256796
30°	95809
35°	52513
40°	34317
45°	20891
50°	13292
55°	9391
60°	6883
65°	3749
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20891 cd/sqm

TEST NUMBER: P752325

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1395.0	24.6
10°-20°	2723.7	48.1
20°-30°	1110.8	19.6
30°-40°	265.8	4.7
40°-50°	110.8	2.0
50°-60°	45.9	0.8
60°-70°	14.4	0.3
70°-80°	0.4	0.0
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5229.6	92.3
0°-40°	5495.4	97.0
0°-60°	5652.1	99.7
0°-90°	5667.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5667.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15593	
5°	15168	###
15°	10288	2724
25°	2130	1111
35°	394	266
45°	135	111
55°	49	46
65°	14	14
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752325

CATALOG NUMBER: LD4D70BD010-EU4DR3570959035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	15592.6
2.5°	15499.1
5°	15168.3
7.5°	14508.4
10°	13514.4
12.5°	12114.7
15°	10288.2
17.5°	8054.4
20°	5676.8
22.5°	3619.9
25°	2130.1
27.5°	1204.1
30°	759.4
32.5°	533.2
35°	393.7
37.5°	304.4
40°	240.6
42.5°	185.4
45°	135.2
47.5°	101.2
50°	78.2
52.5°	62.1
55°	49.3
57.5°	40.0
60°	31.5
62.5°	23.0
65°	14.5
67.5°	5.1
70°	0.9
72.5°	0.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)