

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752642

Luminaire Tested: LD4D70BD010-EU4DR5570959035-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959035-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7378.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752642

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P752642

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75		
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70		
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65		
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61		
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57		
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54		
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	903936
5°	868036
10°	864771
15°	839925
20°	753111
25°	622406
30°	470148
35°	340900
40°	218167
45°	99633
50°	32585
55°	14058
60°	6053
65°	801
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 99633 cd/sqm



TEST NUMBER: P752642

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	753.1	10.2
10°-20°	2055.3	27.9
20°-30°	2342.3	31.7
30°-40°	1594.5	21.6
40°-50°	549.4	7.4
50°-60°	76.0	1.0
60°-70°	7.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5150.7	69.8
0°-40°	6745.2	91.4
0°-60°	7370.6	99.9
0°-90°	7378.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7378.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8273	
5°	7914	753
15°	7425	2055
25°	5163	2342
35°	2556	1595
45°	645	549
55°	74	76
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752642

CATALOG NUMBER: LD4D70BD010-EU4DR5570959035-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	8273.2
2.5°	8083.6
5°	7914.4
7.5°	7831.4
10°	7794.5
12.5°	7671.4
15°	7425.4
17.5°	7034.8
20°	6477.1
22.5°	5833.3
25°	5162.8
27.5°	4464.7
30°	3726.5
32.5°	3101.2
35°	2555.8
37.5°	2037.0
40°	1529.6
42.5°	1060.0
45°	644.8
47.5°	347.5
50°	191.7
52.5°	113.8
55°	73.8
57.5°	47.2
60°	27.7
62.5°	12.3
65°	3.1
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)