

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754099

Luminaire Tested: LD4D80BD010-EU4DR5070959027-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754099
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR5070959027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8469.9 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P754099

CATALOG NUMBER: LD4D80BD010-EU4DR5070959027-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P754099

CATALOG NUMBER: LD4D80BD010-EU4DR5070959027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1491092
5°	1475467
10°	1451166
15°	1321399
20°	1099558
25°	780527
30°	413135
35°	168356
40°	62529
45°	28617
50°	11729
55°	6134
60°	3016
65°	905
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28617 cd/sqm



TEST NUMBER: P754099

CATALOG NUMBER: LD4D80BD010-EU4DR5070959027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1271.5	15.0
10°-20°	3213.5	37.9
20°-30°	2886.6	34.1
30°-40°	903.8	10.7
40°-50°	158.2	1.9
50°-60°	31.5	0.4
60°-70°	4.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7371.6	87.0
0°-40°	8275.3	97.7
0°-60°	8465.1	99.9
0°-90°	8469.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8469.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13647	
5°	13453	###
15°	11682	3213
25°	6474	2887
35°	1262	904
45°	185	158
55°	32	32
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754099

CATALOG NUMBER: LD4D80BD010-EU4DR5070959027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	13647.1
2.5°	13579.2
5°	13452.7
7.5°	13259.4
10°	13079.9
12.5°	12504.6
15°	11681.9
17.5°	10637.2
20°	9456.7
22.5°	8090.9
25°	6474.4
27.5°	4760.0
30°	3274.6
32.5°	2132.0
35°	1262.2
37.5°	724.9
40°	438.4
42.5°	285.3
45°	185.2
47.5°	112.8
50°	69.0
52.5°	47.2
55°	32.2
57.5°	21.9
60°	13.8
62.5°	8.1
65°	3.5
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)