

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752721

Luminaire Tested: LD4D70BD010-EU4DR6070959035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR6070959035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7597.4 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752721

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752721

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	830710
5°	828673
10°	856206
15°	857084
20°	788609
25°	670773
30°	511101
35°	361427
40°	212233
45°	85634
50°	28591
55°	13753
60°	5660
65°	827
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 85634 cd/sqm



TEST NUMBER: P752721

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	728.8	9.6
10°-20°	2099.1	27.6
20°-30°	2512.4	33.1
30°-40°	1680.4	22.1
40°-50°	498.2	6.6
50°-60°	71.6	0.9
60°-70°	6.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5340.4	70.3
0°-40°	7020.7	92.4
0°-60°	7590.5	99.9
0°-90°	7597.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7597.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7603	
5°	7556	729
15°	7577	2099
25°	5564	2512
35°	2710	1680
45°	554	498
55°	72	72
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752721

CATALOG NUMBER: LD4D70BD010-EU4DR6070959035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7603.0
2.5°	7593.3
5°	7555.5
7.5°	7658.0
10°	7717.3
12.5°	7706.5
15°	7577.1
17.5°	7272.0
20°	6782.4
22.5°	6194.7
25°	5564.0
27.5°	4853.4
30°	4051.1
32.5°	3335.1
35°	2709.7
37.5°	2083.2
40°	1488.0
42.5°	981.2
45°	554.2
47.5°	283.6
50°	168.2
52.5°	108.9
55°	72.2
57.5°	46.4
60°	25.9
62.5°	10.8
65°	3.2
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)