

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752184

Luminaire Tested: LD4D70BD010-EU4DR2570959040-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752184
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR2570959040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6731.4 lumens
Efficiency: N/A
Efficacy: 101.1 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752184

CATALOG NUMBER: LD4D70BD010-EU4DR2570959040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752184

CATALOG NUMBER: LD4D70BD010-EU4DR2570959040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2789482
5°	2598044
10°	1853258
15°	1091504
20°	679150
25°	372711
30°	170459
35°	64557
40°	29239
45°	17584
50°	7292
55°	4705
60°	3278
65°	2223
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17584 cd/sqm



TEST NUMBER: P752184

CATALOG NUMBER: LD4D70BD010-EU4DR2570959040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2035.8	30.2
10°-20°	2757.3	41.0
20°-30°	1459.1	21.7
30°-40°	360.2	5.4
40°-50°	87.9	1.3
50°-60°	23.1	0.3
60°-70°	7.8	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6252.3	92.9
0°-40°	6612.5	98.2
0°-60°	6723.5	99.9
0°-90°	6731.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6731.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	25530	
5°	23688	###
15°	9650	2757
25°	3092	1459
35°	484	360
45°	114	88
55°	25	23
65°	9	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752184

CATALOG NUMBER: LD4D70BD010-EU4DR2570959040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	25530.5
2.5°	25110.9
5°	23687.9
7.5°	20829.2
10°	16704.1
12.5°	12627.3
15°	9649.5
17.5°	7520.4
20°	5841.0
22.5°	4380.5
25°	3091.6
27.5°	2073.3
30°	1351.1
32.5°	822.0
35°	484.0
37.5°	296.2
40°	205.0
42.5°	156.7
45°	113.8
47.5°	68.7
50°	42.9
52.5°	31.1
55°	24.7
57.5°	19.3
60°	15.0
62.5°	11.8
65°	8.6
67.5°	3.2
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)