

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752344

Luminaire Tested: LD4D70BD010-EU4DR3570959040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR3570959040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7574.5 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752344

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBS1LI

Luminous Intensity Polar Plot



TEST NUMBER: P752344

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2277125
5°	2223614
10°	2004067
15°	1555479
20°	882244
25°	343235
30°	128056
35°	70186
40°	45870
45°	27921
50°	17780
55°	12553
60°	9200
65°	4990
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27921 cd/sqm



TEST NUMBER: P752344

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1864.6	24.6
10°-20°	3640.5	48.1
20°-30°	1484.8	19.6
30°-40°	355.3	4.7
40°-50°	148.1	2.0
50°-60°	61.3	0.8
60°-70°	19.2	0.3
70°-80°	0.4	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6989.9	92.3
0°-40°	7345.2	97.0
0°-60°	7554.6	99.7
0°-90°	7574.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7574.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	20841	
5°	20274	###
15°	13751	3641
25°	2847	1485
35°	526	355
45°	181	148
55°	66	61
65°	19	19
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752344

CATALOG NUMBER: LD4D70BD010-EU4DR3570959040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	20841.2
2.5°	20716.2
5°	20274.0
7.5°	19392.1
10°	18063.4
12.5°	16192.6
15°	13751.3
17.5°	10765.5
20°	7587.7
22.5°	4838.4
25°	2847.1
27.5°	1609.4
30°	1015.0
32.5°	712.6
35°	526.2
37.5°	406.9
40°	321.6
42.5°	247.8
45°	180.7
47.5°	135.3
50°	104.6
52.5°	83.0
55°	65.9
57.5°	53.4
60°	42.1
62.5°	30.7
65°	19.3
67.5°	6.8
70°	1.1
72.5°	1.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)