

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752495

Luminaire Tested: LD4D70BD010-EU4DR4570959040-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4570959040-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7348.5 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752495

CATALOG NUMBER: LD4D70BD010-EU4DR4570959040-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P752495

CATALOG NUMBER: LD4D70BD010-EU4DR4570959040-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	97	97	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	91	91	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	87	87	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	82	82	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	78	78	77
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	71	71	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	67	67	66
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	64	64	63
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1419155
5°	1378753
10°	1319096
15°	1207243
20°	957763
25°	597945
30°	329564
35°	147988
40°	58279
45°	27473
50°	13020
55°	6820
60°	3343
65°	801
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27473 cd/sqm



TEST NUMBER: P752495

CATALOG NUMBER: LD4D70BD010-EU4DR4570959040-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1181.2	16.1
10°-20°	2907.0	39.6
20°-30°	2302.0	31.3
30°-40°	766.6	10.4
40°-50°	152.1	2.1
50°-60°	34.6	0.5
60°-70°	5.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6390.1	87.0
0°-40°	7156.7	97.4
0°-60°	7343.4	99.9
0°-90°	7348.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7348.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12989	
5°	12571	###
15°	10673	2907
25°	4960	2302
35°	1110	767
45°	178	152
55°	36	35
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752495

CATALOG NUMBER: LD4D70BD010-EU4DR4570959040-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	12988.7
2.5°	12903.9
5°	12570.9
7.5°	12296.1
10°	11889.5
12.5°	11348.0
15°	10672.7
17.5°	9657.2
20°	8237.2
22.5°	6545.4
25°	4959.9
27.5°	3631.8
30°	2612.2
32.5°	1776.6
35°	1109.5
37.5°	657.9
40°	408.6
42.5°	268.7
45°	177.8
47.5°	114.4
50°	76.6
52.5°	51.1
55°	35.8
57.5°	23.5
60°	15.3
62.5°	8.2
65°	3.1
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)