

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752575

Luminaire Tested: LD4D70BD010-EU4DR5070959040-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5070959040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7079.0 lumens
Efficiency: N/A
Efficacy: 106.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752575

CATALOG NUMBER: LD4D70BD010-EU4DR5070959040-4LBDP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P752575

CATALOG NUMBER: LD4D70BD010-EU4DR5070959040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	106	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	90	87	84		89	85	83		87
5	96	89	84	80	95	88	83	79	86	82	79		85	81	78		83
6	92	84	79	75	91	83	79	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	71		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	67	64	71	67	64		71	67	64		70
10	78	70	64	61	77	69	64	61	68	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1246239
5°	1233177
10°	1212865
15°	1104410
20°	918997
25°	652352
30°	345284
35°	140705
40°	52260
45°	23919
50°	9808
55°	5124
60°	2513
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23919 cd/sqm



TEST NUMBER: P752575

CATALOG NUMBER: LD4D70BD010-EU4DR5070959040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1062.7	15.0
10°-20°	2685.8	37.9
20°-30°	2412.5	34.1
30°-40°	755.3	10.7
40°-50°	132.3	1.9
50°-60°	26.4	0.4
60°-70°	4.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6161.1	87.0
0°-40°	6916.4	97.7
0°-60°	7075.0	99.9
0°-90°	7079.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7079.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11406	
5°	11244	###
15°	9764	2686
25°	5411	2413
35°	1055	755
45°	155	132
55°	27	26
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752575

CATALOG NUMBER: LD4D70BD010-EU4DR5070959040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	11406.1
2.5°	11349.3
5°	11243.6
7.5°	11082.0
10°	10932.0
12.5°	10451.2
15°	9763.6
17.5°	8890.4
20°	7903.8
22.5°	6762.3
25°	5411.2
27.5°	3978.3
30°	2736.8
32.5°	1781.9
35°	1054.9
37.5°	605.8
40°	366.4
42.5°	238.5
45°	154.8
47.5°	94.2
50°	57.7
52.5°	39.4
55°	26.9
57.5°	18.3
60°	11.5
62.5°	6.7
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)