

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752654

Luminaire Tested: LD4D70BD010-EU4DR5570959040-4LBS1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959040-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7248.2 lumens
Efficiency: N/A
Efficacy: 108.8 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752654

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P752654

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	888039
5°	852769
10°	849560
15°	825152
20°	739868
25°	611460
30°	461884
35°	334897
40°	214330
45°	97887
50°	32007
55°	13811
60°	5944
65°	776
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 97887 cd/sqm



TEST NUMBER: P752654

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	739.9	10.2
10°-20°	2019.2	27.9
20°-30°	2301.1	31.7
30°-40°	1566.5	21.6
40°-50°	539.8	7.4
50°-60°	74.6	1.0
60°-70°	7.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5060.1	69.8
0°-40°	6626.6	91.4
0°-60°	7241.0	99.9
0°-90°	7248.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7248.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8128	
5°	7775	740
15°	7295	2019
25°	5072	2301
35°	2511	1566
45°	634	540
55°	72	75
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752654

CATALOG NUMBER: LD4D70BD010-EU4DR5570959040-4LBS1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	8127.7
2.5°	7941.4
5°	7775.2
7.5°	7693.7
10°	7657.4
12.5°	7536.5
15°	7294.8
17.5°	6911.1
20°	6363.2
22.5°	5730.7
25°	5072.0
27.5°	4386.2
30°	3661.0
32.5°	3046.6
35°	2510.8
37.5°	2001.2
40°	1502.7
42.5°	1041.4
45°	633.5
47.5°	341.4
50°	188.3
52.5°	111.8
55°	72.5
57.5°	46.3
60°	27.2
62.5°	12.1
65°	3.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)