

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756345

Luminaire Tested: LD4D95BD010-EU4DR4570959024-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756345
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4570959024-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7311.5 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756345

CATALOG NUMBER: LD4D95BD010-EU4DR4570959024-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756345

CATALOG NUMBER: LD4D95BD010-EU4DR4570959024-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108	112	110	108	106		106	104	103		102	101	100		98	98	97
2	109	105	102	99	107	103	100	98		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	91		95	92	89		93	90	88		91	89	87
4	100	94	89	85	99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80	95	88	83	80		86	82	79		85	81	79		83	80	78
6	92	85	80	76	91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	75	72	87	80	75	72		79	74	71		78	74	71		77	73	71
8	85	77	72	68	84	76	71	68		75	71	68		74	70	67		73	70	67
9	82	73	68	65	81	73	68	65		72	68	65		71	67	64		71	67	64
10	79	70	65	62	78	70	65	62		69	65	62		68	64	61		68	64	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1412020
5°	1371821
10°	1312461
15°	1201180
20°	952949
25°	594943
30°	327911
35°	147241
40°	57993
45°	27334
50°	12952
55°	6781
60°	3322
65°	776
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 27334 cd/sqm

TEST NUMBER: P756345

CATALOG NUMBER: LD4D95BD010-EU4DR4570959024-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1175.2	16.1
10°-20°	2892.3	39.6
20°-30°	2290.4	31.3
30°-40°	762.7	10.4
40°-50°	151.4	2.1
50°-60°	34.4	0.5
60°-70°	4.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6358.0	87.0
0°-40°	7120.7	97.4
0°-60°	7306.5	99.9
0°-90°	7311.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7311.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12923	
5°	12508	###
15°	10619	2892
25°	4935	2290
35°	1104	763
45°	177	151
55°	36	34
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756345

CATALOG NUMBER: LD4D95BD010-EU4DR4570959024-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12923.4
2.5°	12839.0
5°	12507.7
7.5°	12234.2
10°	11829.7
12.5°	11290.9
15°	10619.1
17.5°	9608.7
20°	8195.8
22.5°	6512.5
25°	4935.0
27.5°	3613.5
30°	2599.1
32.5°	1767.6
35°	1103.9
37.5°	654.6
40°	406.6
42.5°	267.3
45°	176.9
47.5°	113.8
50°	76.2
52.5°	50.8
55°	35.6
57.5°	23.4
60°	15.2
62.5°	8.1
65°	3.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)