

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756579

Luminaire Tested: LD4D95BD010-EU4DR6070959024-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P756579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D95BD010-EU4DR6070959024-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6851.0 lumens  
Efficiency: N/A  
Efficacy: 69.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight

TEST NUMBER: P756579

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBDP1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P756579

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 |  | 100 | 99  | 97  |  | 97  |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 92  |  | 94  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 90  | 86  | 100 | 94  | 89  | 86  | 91  | 88  | 84  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 89  | 84  | 80  | 95  | 88  | 83  | 79  | 86  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 87  | 78  | 73  | 69  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 7   | 84  | 75  | 69  | 65  | 83  | 74  | 68  | 64  | 73  | 68  | 64  |  | 72  | 67  | 64  |  | 71  |
| 8   | 80  | 71  | 65  | 61  | 79  | 70  | 65  | 61  | 69  | 64  | 60  |  | 68  | 64  | 60  |  | 67  |
| 9   | 77  | 67  | 61  | 57  | 75  | 67  | 61  | 57  | 66  | 61  | 57  |  | 65  | 60  | 57  |  | 64  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 58  | 54  |  | 62  | 57  | 54  |  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 888989 |
| 5°  | 910855 |
| 10° | 921853 |
| 15° | 878191 |
| 20° | 774296 |
| 25° | 626264 |
| 30° | 423619 |
| 35° | 212279 |
| 40° | 34431  |
| 45° | 33700  |
| 50° | 34370  |
| 55° | 34898  |
| 60° | 35859  |
| 65° | 36686  |
| 70° | 37536  |
| 75° | 37994  |
| 80° | 36620  |
| 85° | 30588  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 75°

Luminance: 37994 cd/sqm



TEST NUMBER: P756579

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBDP1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 793.7  | 11.6      |
| 10°-20°   | 2147.5 | 31.3      |
| 20°-30°   | 2310.5 | 33.7      |
| 30°-40°   | 1004.3 | 14.7      |
| 40°-50°   | 168.7  | 2.5       |
| 50°-60°   | 164.0  | 2.4       |
| 60°-70°   | 140.3  | 2.0       |
| 70°-80°   | 93.9   | 1.4       |
| 80°-90°   | 28.1   | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 5251.7 | 76.7      |
| 0°-40°    | 6256.0 | 91.3      |
| 0°-60°    | 6588.7 | 96.2      |
| 0°-90°    | 6851.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 6851.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8136 |      |
| 5°  | 8305 | 794  |
| 15° | 7764 | 2147 |
| 25° | 5195 | 2311 |
| 35° | 1592 | 1004 |
| 45° | 218  | 169  |
| 55° | 183  | 164  |
| 65° | 142  | 140  |
| 75° | 90   | 94   |
| 85° | 24   | 28   |
| 90° | 0    |      |



TEST NUMBER: P756579

CATALOG NUMBER: LD4D95BD010-EU4DR6070959024-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 8136.4 |
| 2.5°  | 8365.1 |
| 5°    | 8304.8 |
| 7.5°  | 8323.8 |
| 10°   | 8309.0 |
| 12.5° | 8137.5 |
| 15°   | 7763.7 |
| 17.5° | 7261.8 |
| 20°   | 6659.3 |
| 22.5° | 6014.4 |
| 25°   | 5194.8 |
| 27.5° | 4155.0 |
| 30°   | 3357.7 |
| 32.5° | 2587.9 |
| 35°   | 1591.5 |
| 37.5° | 680.9  |
| 40°   | 241.4  |
| 42.5° | 222.4  |
| 45°   | 218.1  |
| 47.5° | 210.7  |
| 50°   | 202.2  |
| 52.5° | 192.7  |
| 55°   | 183.2  |
| 57.5° | 173.7  |
| 60°   | 164.1  |
| 62.5° | 153.5  |
| 65°   | 141.9  |
| 67.5° | 130.2  |
| 70°   | 117.5  |
| 72.5° | 103.8  |
| 75°   | 90.0   |
| 77.5° | 74.1   |
| 80°   | 58.2   |
| 82.5° | 41.3   |
| 85°   | 24.4   |
| 87.5° | 8.5    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

## Scaled Data Report





— 0°-180°







(END OF REPORT)