

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752890

Luminaire Tested: LD4D70BD010-EU4DR7070959040-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752890
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR7070959040-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8004.7 lumens
Efficiency: N/A
Efficacy: 120.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752890

CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752890

CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	690309
5°	688592
10°	687101
15°	686902
20°	680185
25°	638958
30°	569628
35°	454168
40°	301562
45°	180292
50°	93472
55°	49127
60°	17372
65°	284
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 180292 cd/sqm



TEST NUMBER: P752890

CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	597.1	7.5
10°-20°	1712.4	21.4
20°-30°	2415.7	30.2
30°-40°	2085.4	26.1
40°-50°	933.9	11.7
50°-60°	244.5	3.1
60°-70°	15.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4725.1	59.0
0°-40°	6810.5	85.1
0°-60°	7988.8	99.8
0°-90°	8004.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8004.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6318	
5°	6278	597
15°	6073	1712
25°	5300	2416
35°	3405	2085
45°	1167	934
55°	258	245
65°	1	16
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752890

CATALOG NUMBER: LD4D70BD010-EU4DR7070959040-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6318.0
2.5°	6311.2
5°	6278.3
7.5°	6251.0
10°	6193.1
12.5°	6140.8
15°	6072.6
17.5°	5994.2
20°	5849.9
22.5°	5612.5
25°	5300.1
27.5°	4937.6
30°	4515.0
32.5°	3998.0
35°	3405.0
37.5°	2750.6
40°	2114.3
42.5°	1606.5
45°	1166.8
47.5°	804.4
50°	549.9
52.5°	379.5
55°	257.9
57.5°	155.7
60°	79.5
62.5°	25.0
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)