

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756738

Luminaire Tested: LD4D95BD010-EU4DR7070959024-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR7070959024-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8416.2 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756738

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756738

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	95	94	93		
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78		
4	95	87	81	76	93	86	80	76	83	78	75	81	77	74	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	84	75	68	63	83	74	68	63	72	67	63	71	66	62	69	65	62	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	61	57	56		
8	75	65	58	54	74	64	58	54	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	53	50	58	53	49	57	53	49	48		
10	67	57	50	46	66	56	50	46	55	50	46	55	50	46	54	49	46	44		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	725797
5°	723985
10°	722416
15°	722217
20°	715148
25°	671798
30°	598911
35°	477510
40°	317066
45°	189563
50°	98282
55°	51661
60°	18268
65°	310
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 189563 cd/sqm



TEST NUMBER: P756738

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	627.7	7.5
10°-20°	1800.4	21.4
20°-30°	2539.8	30.2
30°-40°	2192.6	26.1
40°-50°	981.9	11.7
50°-60°	257.1	3.1
60°-70°	16.7	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4968.0	59.0
0°-40°	7160.5	85.1
0°-60°	8399.5	99.8
0°-90°	8416.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8416.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6643	
5°	6601	628
15°	6385	1800
25°	5572	2540
35°	3580	2193
45°	1227	982
55°	271	257
65°	1	17
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756738

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6642.8
2.5°	6635.6
5°	6601.0
7.5°	6572.3
10°	6511.4
12.5°	6456.4
15°	6384.8
17.5°	6302.3
20°	6150.6
22.5°	5901.0
25°	5572.5
27.5°	5191.4
30°	4747.1
32.5°	4203.6
35°	3580.0
37.5°	2892.0
40°	2223.0
42.5°	1689.1
45°	1226.8
47.5°	845.7
50°	578.2
52.5°	399.0
55°	271.2
57.5°	163.7
60°	83.6
62.5°	26.3
65°	1.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)