

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756206

Luminaire Tested: LD4D95BD010-EU4DR3570959027-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756206
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8167.2 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756206

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756206

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2455330
5°	2397629
10°	2160901
15°	1677202
20°	951286
25°	370095
30°	138073
35°	75681
40°	49464
45°	30116
50°	19157
55°	13544
60°	9899
65°	5377
70°	383
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30116 cd/sqm



TEST NUMBER: P756206

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2010.5	24.6
10°-20°	3925.4	48.1
20°-30°	1600.9	19.6
30°-40°	383.1	4.7
40°-50°	159.7	2.0
50°-60°	66.1	0.8
60°-70°	20.7	0.3
70°-80°	0.5	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7536.9	92.3
0°-40°	7920.0	97.0
0°-60°	8145.8	99.7
0°-90°	8167.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8167.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22472	
5°	21861	###
15°	14827	3925
25°	3070	1601
35°	567	383
45°	195	160
55°	71	66
65°	21	21
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756206

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	22472.2
2.5°	22337.4
5°	21860.6
7.5°	20909.6
10°	19477.0
12.5°	17459.8
15°	14827.4
17.5°	11608.0
20°	8181.5
22.5°	5217.0
25°	3069.9
27.5°	1735.3
30°	1094.4
32.5°	768.4
35°	567.4
37.5°	438.7
40°	346.8
42.5°	267.2
45°	194.9
47.5°	145.8
50°	112.7
52.5°	89.5
55°	71.1
57.5°	57.6
60°	45.3
62.5°	33.1
65°	20.8
67.5°	7.4
70°	1.2
72.5°	1.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)