

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752512

Luminaire Tested: LD4D70BD010-EU4DR4570959050-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR4570959050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7790.5 lumens
Efficiency: N/A
Efficacy: 117.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752512

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P752512

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1504521
5°	1461680
10°	1398433
15°	1279863
20°	1015376
25°	633907
30°	349397
35°	156885
40°	61787
45°	29127
50°	13802
55°	7220
60°	3540
65°	827
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29127 cd/sqm



TEST NUMBER: P752512

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1252.2	16.1
10°-20°	3081.8	39.6
20°-30°	2440.5	31.3
30°-40°	812.7	10.4
40°-50°	161.3	2.1
50°-60°	36.6	0.5
60°-70°	5.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6774.5	87.0
0°-40°	7587.2	97.4
0°-60°	7785.1	99.9
0°-90°	7790.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7790.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13770	
5°	13327	###
15°	11315	3082
25°	5258	2440
35°	1176	813
45°	188	161
55°	38	37
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752512

CATALOG NUMBER: LD4D70BD010-EU4DR4570959050-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	13770.0
2.5°	13680.1
5°	13327.0
7.5°	13035.7
10°	12604.6
12.5°	12030.6
15°	11314.7
17.5°	10238.1
20°	8732.7
22.5°	6939.1
25°	5258.2
27.5°	3850.3
30°	2769.4
32.5°	1883.4
35°	1176.2
37.5°	697.5
40°	433.2
42.5°	284.8
45°	188.5
47.5°	121.3
50°	81.2
52.5°	54.2
55°	37.9
57.5°	24.9
60°	16.2
62.5°	8.7
65°	3.2
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)