

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752666

Luminaire Tested: LD4D70BD010-EU4DR5570959050-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959050-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6764.4 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752666

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P752666

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64		82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	828765
5°	795857
10°	792855
15°	770076
20°	690486
25°	570651
30°	431063
35°	312542
40°	200024
45°	91351
50°	29882
55°	12896
60°	5550
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 91351 cd/sqm



TEST NUMBER: P752666

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	690.5	10.2
10°-20°	1884.4	27.9
20°-30°	2147.5	31.7
30°-40°	1461.9	21.6
40°-50°	503.8	7.4
50°-60°	69.6	1.0
60°-70°	6.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4722.4	69.8
0°-40°	6184.3	91.4
0°-60°	6757.7	99.9
0°-90°	6764.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6764.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7585	
5°	7256	690
15°	6808	1884
25°	4734	2147
35°	2343	1462
45°	591	504
55°	68	70
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752666

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7585.2
2.5°	7411.4
5°	7256.3
7.5°	7180.1
10°	7146.3
12.5°	7033.5
15°	6807.9
17.5°	6449.8
20°	5938.5
22.5°	5348.2
25°	4733.5
27.5°	4093.4
30°	3416.7
32.5°	2843.3
35°	2343.2
37.5°	1867.6
40°	1402.4
42.5°	971.9
45°	591.2
47.5°	318.6
50°	175.8
52.5°	104.3
55°	67.7
57.5°	43.2
60°	25.4
62.5°	11.3
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)