

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756433

Luminaire Tested: LD4D95BD010-EU4DR5070959027-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7904.6 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756433

CATALOG NUMBER: LD4D95BD010-EU4DR5070959027-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P756433

CATALOG NUMBER: LD4D95BD010-EU4DR5070959027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			98
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			95
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			91
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			87
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			83
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			79
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			76
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			73
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			70
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1391578
5°	1376987
10°	1354310
15°	1233203
20°	1026166
25°	728423
30°	385556
35°	157125
40°	58350
45°	26716
50°	10947
55°	5734
60°	2819
65°	827
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26716 cd/sqm



TEST NUMBER: P756433

CATALOG NUMBER: LD4D95BD010-EU4DR5070959027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1186.7	15.0
10°-20°	2999.0	37.9
20°-30°	2693.9	34.1
30°-40°	843.4	10.7
40°-50°	147.7	1.9
50°-60°	29.4	0.4
60°-70°	4.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6879.6	87.0
0°-40°	7723.0	97.7
0°-60°	7900.1	99.9
0°-90°	7904.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7904.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12736	
5°	12555	###
15°	10902	2999
25°	6042	2694
35°	1178	843
45°	173	148
55°	30	29
65°	3	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756433

CATALOG NUMBER: LD4D95BD010-EU4DR5070959027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	12736.3
2.5°	12672.9
5°	12554.8
7.5°	12374.4
10°	12206.9
12.5°	11670.0
15°	10902.2
17.5°	9927.2
20°	8825.5
22.5°	7550.9
25°	6042.2
27.5°	4442.3
30°	3056.0
32.5°	1989.7
35°	1178.0
37.5°	676.5
40°	409.1
42.5°	266.3
45°	172.9
47.5°	105.2
50°	64.4
52.5°	44.0
55°	30.1
57.5°	20.4
60°	12.9
62.5°	7.5
65°	3.2
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)