

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P752669

Luminaire Tested: LD4D70BD010-EU4DR5570959050-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P752669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D70BD010-EU4DR5570959050-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8166.9 lumens
Efficiency: N/A
Efficacy: 122.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 66.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P752669

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P752669

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1000610
5°	960868
10°	957244
15°	929749
20°	833653
25°	688965
30°	520424
35°	377353
40°	241486
45°	110295
50°	36070
55°	15563
60°	6687
65°	879
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 110295 cd/sqm



TEST NUMBER: P752669

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	833.6	10.2
10°-20°	2275.1	27.9
20°-30°	2592.7	31.7
30°-40°	1765.0	21.6
40°-50°	608.2	7.4
50°-60°	84.1	1.0
60°-70°	8.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5701.5	69.8
0°-40°	7466.5	91.4
0°-60°	8158.8	99.9
0°-90°	8166.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8166.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9158	
5°	8761	834
15°	8220	2275
25°	5715	2593
35°	2829	1765
45°	714	608
55°	82	84
65°	3	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P752669

CATALOG NUMBER: LD4D70BD010-EU4DR5570959050-4LBS1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	9158.0
2.5°	8948.0
5°	8760.8
7.5°	8668.8
10°	8628.0
12.5°	8491.8
15°	8219.5
17.5°	7787.1
20°	7169.8
22.5°	6457.1
25°	5714.9
27.5°	4942.1
30°	4125.0
32.5°	3432.8
35°	2829.1
37.5°	2254.9
40°	1693.1
42.5°	1173.4
45°	713.8
47.5°	384.7
50°	212.2
52.5°	126.0
55°	81.7
57.5°	52.2
60°	30.6
62.5°	13.6
65°	3.4
67.5°	1.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)