

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756511

Luminaire Tested: LD4D95BD010-EU4DR5570959027-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959027-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6889.8 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756511

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P756511

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106	111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96	106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87	100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80	95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74	91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68	86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64	82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59	78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56	74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52	71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	844138
5°	810609
10°	807556
15°	784351
20°	703288
25°	581224
30°	439049
35°	318345
40°	203732
45°	93051
50°	30426
55°	13125
60°	5638
65°	750
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 93051 cd/sqm



TEST NUMBER: P756511

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	703.3	10.2
10°-20°	1919.4	27.9
20°-30°	2187.3	31.7
30°-40°	1489.0	21.6
40°-50°	513.1	7.4
50°-60°	70.9	1.0
60°-70°	6.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4809.9	69.8
0°-40°	6298.9	91.4
0°-60°	6883.0	99.9
0°-90°	6889.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6889.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7726	
5°	7391	703
15°	6934	1919
25°	4821	2187
35°	2387	1489
45°	602	513
55°	69	71
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756511

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7725.9
2.5°	7548.7
5°	7390.8
7.5°	7313.2
10°	7278.8
12.5°	7163.9
15°	6934.1
17.5°	6569.4
20°	6048.6
22.5°	5447.3
25°	4821.2
27.5°	4169.3
30°	3480.0
32.5°	2896.0
35°	2386.7
37.5°	1902.3
40°	1428.4
42.5°	989.9
45°	602.2
47.5°	324.5
50°	179.0
52.5°	106.3
55°	68.9
57.5°	44.0
60°	25.8
62.5°	11.5
65°	2.9
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)