

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753534

Luminaire Tested: LD4D75BD010-EU4DR6570959024-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P753534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR6570959024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4009.6 lumens
Efficiency: N/A
Efficacy: 55.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753534

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P753534

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	111	108	106		111	108	106	104		104	103	101		101	99	98		97	96	95
2	108	103	99	95		106	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	89	84	79		95	88	83	79		86	82	78		84	80	77		82	79	76
5	92	83	78	73		90	83	77	73		81	76	72		79	75	72		77	74	71
6	87	78	72	68		86	77	72	68		76	71	67		74	70	67		73	69	66
7	83	73	67	63		81	73	67	63		71	66	62		70	66	62		69	65	62
8	79	69	63	59		77	68	63	59		67	62	58		66	62	58		65	61	58
9	75	65	59	55		74	65	59	55		64	58	55		63	58	55		62	58	54
10	71	61	56	52		70	61	55	52		60	55	51		59	55	51		59	54	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	431340
5°	431693
10°	446892
15°	447630
20°	412118
25°	351143
30°	268816
35°	189910
40°	112107
45°	45506
50°	16505
55°	9182
60°	5266
65°	2896
70°	3035
75°	2364
80°	2454
85°	2131

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45506 cd/sqm



TEST NUMBER: P753534

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	380.1	9.5
10°-20°	1096.5	27.3
20°-30°	1315.6	32.8
30°-40°	884.1	22.1
40°-50°	264.7	6.6
50°-60°	46.7	1.2
60°-70°	13.3	0.3
70°-80°	6.5	0.2
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2792.3	69.6
0°-40°	3676.4	91.7
0°-60°	3987.8	99.5
0°-90°	4009.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4009.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3948	
5°	3936	380
15°	3957	1097
25°	2913	1316
35°	1424	884
45°	294	265
55°	48	47
65°	11	13
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P753534

CATALOG NUMBER: LD4D75BD010-EU4DR6570959024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	3947.8
2.5°	3964.6
5°	3936.0
7.5°	3995.5
10°	4028.0
12.5°	4020.2
15°	3957.3
17.5°	3803.6
20°	3544.4
22.5°	3239.3
25°	2912.7
27.5°	2544.2
30°	2130.7
32.5°	1756.0
35°	1423.8
37.5°	1095.6
40°	786.0
42.5°	513.3
45°	294.5
47.5°	156.0
50°	97.1
52.5°	67.3
55°	48.2
57.5°	34.8
60°	24.1
62.5°	15.7
65°	11.2
67.5°	10.1
70°	9.5
72.5°	7.3
75°	5.6
77.5°	5.0
80°	3.9
82.5°	2.8
85°	1.7
87.5°	1.1
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)