

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P753289

Luminaire Tested: LD4D75BD010-EU4DR4570959050-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P753289
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D75BD010-EU4DR4570959050-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8213.5 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 72.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P753289

CATALOG NUMBER: LD4D75BD010-EU4DR4570959050-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P753289

CATALOG NUMBER: LD4D75BD010-EU4DR4570959050-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1586193
5°	1541032
10°	1474354
15°	1349350
20°	1070501
25°	668326
30°	368359
35°	165408
40°	65139
45°	30703
50°	14550
55°	7620
60°	3737
65°	879
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30703 cd/sqm

TEST NUMBER: P753289

CATALOG NUMBER: LD4D75BD010-EU4DR4570959050-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1320.2	16.1
10°-20°	3249.1	39.6
20°-30°	2573.0	31.3
30°-40°	856.8	10.4
40°-50°	170.0	2.1
50°-60°	38.6	0.5
60°-70°	5.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7142.3	87.0
0°-40°	7999.1	97.4
0°-60°	8207.8	99.9
0°-90°	8213.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8213.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14518	
5°	14050	###
15°	11929	3249
25°	5544	2573
35°	1240	857
45°	199	170
55°	40	39
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P753289

CATALOG NUMBER: LD4D75BD010-EU4DR4570959050-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	14517.5
2.5°	14422.8
5°	14050.5
7.5°	13743.4
10°	13288.9
12.5°	12683.7
15°	11929.0
17.5°	10793.9
20°	9206.8
22.5°	7315.9
25°	5543.7
27.5°	4059.3
30°	2919.7
32.5°	1985.7
35°	1240.1
37.5°	735.4
40°	456.7
42.5°	300.3
45°	198.7
47.5°	127.9
50°	85.6
52.5°	57.1
55°	40.0
57.5°	26.3
60°	17.1
62.5°	9.1
65°	3.4
67.5°	1.1
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)