

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P754438

Luminaire Tested: LD4D80BD010-EU4DR7070959035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P754438
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D80BD010-EU4DR7070959035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7759.5 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 78.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P754438

CATALOG NUMBER: LD4D80BD010-EU4DR7070959035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P754438

CATALOG NUMBER: LD4D80BD010-EU4DR7070959035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	669167
5°	667501
10°	666055
15°	665863
20°	659360
25°	619380
30°	552180
35°	440256
40°	292334
45°	174775
50°	90599
55°	47623
60°	16848
65°	284
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 174775 cd/sqm



TEST NUMBER: P754438

CATALOG NUMBER: LD4D80BD010-EU4DR7070959035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	578.8	7.5
10°-20°	1659.9	21.4
20°-30°	2341.7	30.2
30°-40°	2021.5	26.1
40°-50°	905.3	11.7
50°-60°	237.0	3.1
60°-70°	15.4	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4580.4	59.0
0°-40°	6601.9	85.1
0°-60°	7744.1	99.8
0°-90°	7759.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7759.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6124	
5°	6086	579
15°	5887	1660
25°	5138	2342
35°	3301	2021
45°	1131	905
55°	250	237
65°	1	15
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P754438

CATALOG NUMBER: LD4D80BD010-EU4DR7070959035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6124.5
2.5°	6117.9
5°	6086.0
7.5°	6059.6
10°	6003.4
12.5°	5952.7
15°	5886.6
17.5°	5810.7
20°	5670.8
22.5°	5440.6
25°	5137.7
27.5°	4786.4
30°	4376.7
32.5°	3875.6
35°	3300.7
37.5°	2666.3
40°	2049.6
42.5°	1557.3
45°	1131.1
47.5°	779.7
50°	533.0
52.5°	367.8
55°	250.0
57.5°	150.9
60°	77.1
62.5°	24.2
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)