

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756214

Luminaire Tested: LD4D95BD010-EU4DR3570959030-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756214
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8829.2 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756214

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P756214

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	101	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	105	100	96	93	97	95	92		95	93	91		93
4	103	97	92	89	101	96	92	89	94	90	88		92	89	87		90
5	99	93	88	85	98	92	87	84	90	86	84		89	85	83		87
6	96	89	84	81	94	88	84	81	87	83	80		85	82	80		84
7	93	85	81	78	91	85	80	77	84	80	77		83	79	77		82
8	90	82	78	74	88	82	77	74	81	77	74		80	76	74		79
9	87	79	75	72	86	79	75	72	78	74	71		77	74	71		77
10	84	77	72	69	83	76	72	69	76	72	69		75	71	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2654326
5°	2591957
10°	2336040
15°	1813144
20°	1028387
25°	400089
30°	149264
35°	81817
40°	53472
45°	32541
50°	20721
55°	14630
60°	10708
65°	5817
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32541 cd/sqm



TEST NUMBER: P756214

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2173.5	24.6
10°-20°	4243.6	48.1
20°-30°	1730.7	19.6
30°-40°	414.2	4.7
40°-50°	172.6	2.0
50°-60°	71.4	0.8
60°-70°	22.3	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8147.8	92.3
0°-40°	8561.9	97.0
0°-60°	8806.0	99.7
0°-90°	8829.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8829.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	24294	
5°	23632	###
15°	16029	4244
25°	3319	1731
35°	613	414
45°	211	173
55°	77	71
65°	22	22
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P756214

CATALOG NUMBER: LD4D95BD010-EU4DR3570959030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	24293.5
2.5°	24147.8
5°	23632.4
7.5°	22604.3
10°	21055.6
12.5°	18874.9
15°	16029.2
17.5°	12548.8
20°	8844.6
22.5°	5639.8
25°	3318.7
27.5°	1876.0
30°	1183.1
32.5°	830.7
35°	613.4
37.5°	474.3
40°	374.9
42.5°	288.8
45°	210.6
47.5°	157.7
50°	121.9
52.5°	96.7
55°	76.8
57.5°	62.3
60°	49.0
62.5°	35.8
65°	22.5
67.5°	7.9
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)