

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756296

Luminaire Tested: LD4D95BD010-EU4DR4070959030-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4070959030-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10157.7 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756296

CATALOG NUMBER: LD4D95BD010-EU4DR4070959030-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756296

CATALOG NUMBER: LD4D95BD010-EU4DR4070959030-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		76	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2583995
5°	2571447
10°	2430578
15°	2066295
20°	1408332
25°	587614
30°	184766
35°	85872
40°	47496
45°	21772
50°	10573
55°	5791
60°	3016
65°	1060
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21772 cd/sqm



TEST NUMBER: P756296

CATALOG NUMBER: LD4D95BD010-EU4DR4070959030-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2189.2	21.6
10°-20°	4904.4	48.3
20°-30°	2455.0	24.2
30°-40°	450.0	4.4
40°-50°	124.2	1.2
50°-60°	29.2	0.3
60°-70°	5.6	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9548.6	94.0
0°-40°	9998.6	98.4
0°-60°	10152.0	99.9
0°-90°	10157.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10157.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23650	
5°	23445	###
15°	18267	4904
25°	4874	2455
35°	644	450
45°	141	124
55°	30	29
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756296

CATALOG NUMBER: LD4D95BD010-EU4DR4070959030-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	23649.8
2.5°	23615.3
5°	23445.4
7.5°	22903.8
10°	21907.7
12.5°	20354.8
15°	18267.2
17.5°	15552.4
20°	12112.3
22.5°	8257.7
25°	4874.2
27.5°	2576.6
30°	1464.5
32.5°	946.4
35°	643.8
37.5°	460.1
40°	333.0
42.5°	228.0
45°	140.9
47.5°	89.8
50°	62.2
52.5°	44.2
55°	30.4
57.5°	19.3
60°	13.8
62.5°	8.3
65°	4.1
67.5°	2.8
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)