

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756375

Luminaire Tested: LD4D95BD010-EU4DR4570959030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756375
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4570959030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9012.2 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756375

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P756375

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90		
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73		
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66		
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63		
10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1740436
5°	1690886
10°	1617719
15°	1480552
20°	1174588
25°	733317
30°	404177
35°	181481
40°	71486
45°	33685
50°	15978
55°	8363
60°	4108
65°	982
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33685 cd/sqm



TEST NUMBER: P756375

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1448.6	16.1
10°-20°	3565.1	39.6
20°-30°	2823.2	31.3
30°-40°	940.2	10.4
40°-50°	186.6	2.1
50°-60°	42.4	0.5
60°-70°	6.1	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7836.8	87.0
0°-40°	8777.0	97.4
0°-60°	9005.9	99.9
0°-90°	9012.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9012.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15929	
5°	15417	###
15°	13089	3565
25°	6083	2823
35°	1361	940
45°	218	187
55°	44	42
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756375

CATALOG NUMBER: LD4D95BD010-EU4DR4570959030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	15929.2
2.5°	15825.2
5°	15416.8
7.5°	15079.8
10°	14581.1
12.5°	13917.1
15°	13088.9
17.5°	11843.6
20°	10102.0
22.5°	8027.3
25°	6082.8
27.5°	4454.0
30°	3203.6
32.5°	2178.8
35°	1360.6
37.5°	806.9
40°	501.2
42.5°	329.5
45°	218.0
47.5°	140.3
50°	94.0
52.5°	62.6
55°	43.9
57.5°	28.8
60°	18.8
62.5°	10.0
65°	3.8
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)