

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756524

Luminaire Tested: LD4D95BD010-EU4DR5570959030-4LBDP1B

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756524
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7098.0 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756524

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBDP1B

Luminous Intensity Polar Plot



TEST NUMBER: P756524

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106	111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96	106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87	100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80	95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74	91	83	77	73		81	76	73		79	75	72		78	74	71
6	88	79	73	68	86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	64	82	73	67	63		72	67	63		71	66	63		70	65	62
8	79	69	63	59	78	69	63	59		68	63	59		67	62	59		66	62	58
9	75	66	60	56	74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52	71	61	56	52		61	56	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	869639
5°	835100
10°	831953
15°	808060
20°	724543
25°	598789
30°	452309
35°	327962
40°	209880
45°	95863
50°	31344
55°	13525
60°	5813
65°	776
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 95863 cd/sqm



TEST NUMBER: P756524

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	724.5	10.2
10°-20°	1977.4	27.9
20°-30°	2253.4	31.7
30°-40°	1534.0	21.6
40°-50°	528.6	7.4
50°-60°	73.1	1.0
60°-70°	7.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4955.3	69.8
0°-40°	6489.3	91.4
0°-60°	7091.0	99.9
0°-90°	7098.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7098.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7959	
5°	7614	725
15°	7144	1977
25°	4967	2253
35°	2459	1534
45°	620	529
55°	71	73
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756524

CATALOG NUMBER: LD4D95BD010-EU4DR5570959030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	7959.3
2.5°	7776.9
5°	7614.1
7.5°	7534.2
10°	7498.7
12.5°	7380.4
15°	7143.7
17.5°	6767.9
20°	6231.4
22.5°	5612.0
25°	4966.9
27.5°	4295.3
30°	3585.1
32.5°	2983.5
35°	2458.8
37.5°	1959.7
40°	1471.5
42.5°	1019.8
45°	620.4
47.5°	334.4
50°	184.4
52.5°	109.5
55°	71.0
57.5°	45.4
60°	26.6
62.5°	11.8
65°	3.0
67.5°	1.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)