

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756266

Luminaire Tested: LD4D95BD010-EU4DR4070959024-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4070959024-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8268.8 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756266

CATALOG NUMBER: LD4D95BD010-EU4DR4070959024-4LBDP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P756266

CATALOG NUMBER: LD4D95BD010-EU4DR4070959024-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93
4	102	97	92	89	101	95	91	88	93	90	87		92	89	86		90
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	83	76	71	68	82	75	71	68	75	71	68		74	70	68		73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2103488
5°	2093273
10°	1978594
15°	1682055
20°	1146439
25°	478342
30°	150399
35°	69906
40°	38653
45°	17723
50°	8601
55°	4705
60°	2447
65°	879
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17723 cd/sqm

TEST NUMBER: P756266

CATALOG NUMBER: LD4D95BD010-EU4DR4070959024-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1782.1	21.6
10°-20°	3992.4	48.3
20°-30°	1998.5	24.2
30°-40°	366.3	4.4
40°-50°	101.1	1.2
50°-60°	23.7	0.3
60°-70°	4.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7773.0	94.0
0°-40°	8139.3	98.4
0°-60°	8264.1	99.9
0°-90°	8268.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8268.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19252	
5°	19086	###
15°	14870	3992
25°	3968	1998
35°	524	366
45°	115	101
55°	25	24
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756266

CATALOG NUMBER: LD4D95BD010-EU4DR4070959024-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	19252.0
2.5°	19223.9
5°	19085.6
7.5°	18644.7
10°	17833.8
12.5°	16569.7
15°	14870.3
17.5°	12660.4
20°	9859.9
22.5°	6722.1
25°	3967.8
27.5°	2097.5
30°	1192.1
32.5°	770.4
35°	524.1
37.5°	374.5
40°	271.0
42.5°	185.6
45°	114.7
47.5°	73.1
50°	50.6
52.5°	36.0
55°	24.7
57.5°	15.7
60°	11.2
62.5°	6.7
65°	3.4
67.5°	2.2
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)