

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756607

Luminaire Tested: LD4D95BD010-EU4DR6070959030-4LBS1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6070959030-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9293.2 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756607

CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P756607

CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1016125
5°	1013645
10°	1047311
15°	1048384
20°	964635
25°	820479
30°	625178
35°	442097
40°	259615
45°	104748
50°	34982
55°	16839
60°	6927
65°	1034
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 104748 cd/sqm



TEST NUMBER: P756607

CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	891.5	9.6
10°-20°	2567.6	27.6
20°-30°	3073.1	33.1
30°-40°	2055.4	22.1
40°-50°	609.4	6.6
50°-60°	87.6	0.9
60°-70°	8.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6532.3	70.3
0°-40°	8587.8	92.4
0°-60°	9284.8	99.9
0°-90°	9293.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9293.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9300	
5°	9242	892
15°	9268	2568
25°	6806	3073
35°	3314	2055
45°	678	609
55°	88	88
65°	4	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756607

CATALOG NUMBER: LD4D95BD010-EU4DR6070959030-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9300.0
2.5°	9288.1
5°	9242.0
7.5°	9367.3
10°	9439.8
12.5°	9426.6
15°	9268.3
17.5°	8895.1
20°	8296.3
22.5°	7577.4
25°	6805.8
27.5°	5936.6
30°	4955.3
32.5°	4079.5
35°	3314.5
37.5°	2548.2
40°	1820.2
42.5°	1200.3
45°	677.9
47.5°	346.9
50°	205.8
52.5°	133.2
55°	88.4
57.5°	56.7
60°	31.7
62.5°	13.2
65°	4.0
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)