

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756732

Luminaire Tested: LD4D95BD010-EU4DR7070959024-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P756732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR7070959024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4430.4 lumens
Efficiency: N/A
Efficacy: 44.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756732

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P756732

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	74	69	87	79	73	69	77	72	68		75	71	67		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	77	66	60	56	75	66	60	56	65	59	55		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	70	59	53	49	69	59	53	49	58	53	49		57	52	49		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	544228
5°	528056
10°	513337
15°	506608
20°	473068
25°	355387
30°	251229
35°	88993
40°	46797
45°	49848
50°	51606
55°	52575
60°	52904
65°	51784
70°	48877
75°	45297
80°	40206
85°	32594

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 57.5°

Luminance: 52912 cd/sqm



TEST NUMBER: P756732

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	454.1	10.3
10°-20°	1245.6	28.1
20°-30°	1371.9	31.0
30°-40°	524.2	11.8
40°-50°	247.5	5.6
50°-60°	246.0	5.6
60°-70°	197.0	4.4
70°-80°	113.2	2.6
80°-90°	30.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3071.6	69.3
0°-40°	3595.8	81.2
0°-60°	4089.4	92.3
0°-90°	4430.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4430.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4981	
5°	4815	454
15°	4479	1246
25°	2948	1372
35°	667	524
45°	323	248
55°	276	246
65°	200	197
75°	107	113
85°	26	31
90°	0	



TEST NUMBER: P756732

CATALOG NUMBER: LD4D95BD010-EU4DR7070959024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	4981.0
2.5°	4929.0
5°	4814.6
7.5°	4719.2
10°	4626.9
12.5°	4548.8
15°	4478.7
17.5°	4309.1
20°	4068.6
22.5°	3549.6
25°	2947.9
27.5°	2566.2
30°	1991.3
32.5°	1286.3
35°	667.2
37.5°	360.4
40°	328.1
42.5°	325.7
45°	322.6
47.5°	315.5
50°	303.6
52.5°	290.2
55°	276.0
57.5°	260.2
60°	242.1
62.5°	221.6
65°	200.3
67.5°	176.7
70°	153.0
72.5°	129.3
75°	107.3
77.5°	84.4
80°	63.9
82.5°	45.0
85°	26.0
87.5°	10.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)