

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756305

Luminaire Tested: LD4D95BD010-EU4DR4070959035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4070959035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9751.5 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756305

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756305

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	97
2	110	106	103	100		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		104	100	96	93		97	94	92		95	93	90		93	91	89
4	102	97	92	89		101	95	91	88		93	90	87		92	89	86		90	87	85
5	99	92	88	84		97	91	87	84		90	86	83		88	85	83		87	84	82
6	95	88	84	80		94	88	83	80		86	82	80		85	82	79		84	81	79
7	92	85	80	77		91	84	80	77		83	79	76		82	79	76		81	78	76
8	89	82	77	74		88	81	77	74		80	76	73		79	76	73		78	75	73
9	86	79	74	71		85	78	74	71		77	73	71		76	73	70		76	72	70
10	83	76	71	68		82	75	71	68		75	71	68		74	70	68		73	70	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2480656
5°	2468602
10°	2333367
15°	1983653
20°	1352009
25°	564117
30°	177373
35°	82444
40°	45584
45°	20906
50°	10148
55°	5562
60°	2906
65°	1034
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20906 cd/sqm



TEST NUMBER: P756305

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2101.6	21.6
10°-20°	4708.3	48.3
20°-30°	2356.8	24.2
30°-40°	432.0	4.4
40°-50°	119.2	1.2
50°-60°	28.0	0.3
60°-70°	5.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9166.7	94.0
0°-40°	9598.7	98.4
0°-60°	9745.9	99.9
0°-90°	9751.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9751.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	22704	
5°	22508	###
15°	17537	4708
25°	4679	2357
35°	618	432
45°	135	119
55°	29	28
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756305

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	22704.0
2.5°	22670.8
5°	22507.7
7.5°	21987.8
10°	21031.5
12.5°	19540.7
15°	17536.6
17.5°	14930.4
20°	11627.9
22.5°	7927.4
25°	4679.3
27.5°	2473.6
30°	1405.9
32.5°	908.5
35°	618.1
37.5°	441.7
40°	319.6
42.5°	218.8
45°	135.3
47.5°	86.2
50°	59.7
52.5°	42.4
55°	29.2
57.5°	18.6
60°	13.3
62.5°	8.0
65°	4.0
67.5°	2.7
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)