

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756309

Luminaire Tested: LD4D95BD010-EU4DR4070959035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4070959035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10264.7 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756309

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756309

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	115	112	110	108	112	110	108	107		106	105	103			103	101	100			96
2	110	106	103	100	108	105	102	99		102	99	97			99	97	95			92
3	106	101	97	94	104	100	96	93		97	94	92			95	93	90			88
4	102	97	92	89	101	95	91	88		93	90	87			92	89	86			84
5	99	92	88	84	97	91	87	84		90	86	83			88	85	83			81
6	95	88	84	80	94	88	83	80		86	82	80			85	82	79			77
7	92	85	80	77	91	84	80	77		83	79	76			82	79	76			74
8	89	82	77	74	88	81	77	74		80	76	73			79	76	73			72
9	86	79	74	71	85	78	74	71		77	73	71			76	73	70			69
10	83	76	71	68	82	75	71	68		75	71	68			74	70	68			67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2611212
5°	2598527
10°	2456173
15°	2088059
20°	1423168
25°	593798
30°	186709
35°	86779
40°	47995
45°	22003
50°	10675
55°	5848
60°	3059
65°	1086
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22003 cd/sqm



TEST NUMBER: P756309

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2212.3	21.6
10°-20°	4956.1	48.3
20°-30°	2480.8	24.2
30°-40°	454.8	4.4
40°-50°	125.5	1.2
50°-60°	29.5	0.3
60°-70°	5.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9649.2	94.0
0°-40°	10103.9	98.4
0°-60°	10258.9	99.9
0°-90°	10264.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10264.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23899	
5°	23692	###
15°	18460	4956
25°	4926	2481
35°	651	455
45°	142	125
55°	31	29
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756309

CATALOG NUMBER: LD4D95BD010-EU4DR4070959035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	23898.9
2.5°	23864.0
5°	23692.3
7.5°	23145.0
10°	22138.4
12.5°	20569.2
15°	18459.6
17.5°	15716.2
20°	12239.9
22.5°	8344.7
25°	4925.5
27.5°	2603.8
30°	1479.9
32.5°	956.3
35°	650.6
37.5°	464.9
40°	336.5
42.5°	230.4
45°	142.4
47.5°	90.7
50°	62.8
52.5°	44.7
55°	30.7
57.5°	19.5
60°	14.0
62.5°	8.4
65°	4.2
67.5°	2.8
70°	1.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)