

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756383

Luminaire Tested: LD4D95BD010-EU4DR4570959035-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR4570959035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 45° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9567.2 lumens
Efficiency: N/A
Efficacy: 96.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756383

CATALOG NUMBER: LD4D95BD010-EU4DR4570959035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756383

CATALOG NUMBER: LD4D95BD010-EU4DR4570959035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		98
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	91	103	98	94	91	95	92	89		93	90	88		91
4	100	94	89	85	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	83	80	86	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	77	75		80
7	89	81	75	72	87	80	75	72	79	74	71		78	74	71		77
8	85	77	72	68	84	76	71	68	75	71	68		74	70	67		73
9	82	73	68	65	81	73	68	65	72	68	65		71	67	64		71
10	79	70	65	62	78	70	65	62	69	65	62		68	64	61		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1847621
5°	1795014
10°	1717349
15°	1571734
20°	1246933
25°	778478
30°	429069
35°	192658
40°	75879
45°	35755
50°	16964
55°	8877
60°	4370
65°	1034
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35755 cd/sqm

TEST NUMBER: P756383

CATALOG NUMBER: LD4D95BD010-EU4DR4570959035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1537.8	16.1
10°-20°	3784.6	39.6
20°-30°	2997.0	31.3
30°-40°	998.1	10.4
40°-50°	198.1	2.1
50°-60°	45.0	0.5
60°-70°	6.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8319.4	87.0
0°-40°	9317.5	97.4
0°-60°	9560.6	99.9
0°-90°	9567.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9567.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16910	
5°	16366	###
15°	13895	3785
25°	6457	2997
35°	1444	998
45°	231	198
55°	47	45
65°	4	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756383

CATALOG NUMBER: LD4D95BD010-EU4DR4570959035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	16910.2
2.5°	16799.8
5°	16366.2
7.5°	16008.5
10°	15479.1
12.5°	14774.2
15°	13895.0
17.5°	12572.9
20°	10724.2
22.5°	8521.6
25°	6457.4
27.5°	4728.3
30°	3400.9
32.5°	2313.0
35°	1444.4
37.5°	856.6
40°	532.0
42.5°	349.8
45°	231.4
47.5°	149.0
50°	99.8
52.5°	66.5
55°	46.6
57.5°	30.6
60°	20.0
62.5°	10.6
65°	4.0
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)