

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756466

Luminaire Tested: LD4D95BD010-EU4DR5070959035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5070959035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9228.3 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756466

CATALOG NUMBER: LD4D95BD010-EU4DR5070959035-4LBS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P756466

CATALOG NUMBER: LD4D95BD010-EU4DR5070959035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	112	109	107	112	110	108	106		106	104	102			102	101	99			95
2	109	105	101	98	107	103	100	97		100	98	95			97	95	93			90
3	105	99	95	91	103	98	94	90		95	92	89			93	90	88			85
4	100	94	89	85	99	93	88	85		90	87	84			89	85	83			80
5	96	89	84	80	95	88	83	79		86	82	79			85	81	78			76
6	92	84	79	75	91	83	79	75		82	78	74			81	77	74			72
7	88	80	75	71	87	79	74	71		78	74	71			77	73	70			69
8	85	76	71	67	84	76	71	67		75	70	67			74	70	67			65
9	81	73	68	64	80	72	67	64		71	67	64			71	67	64			62
10	78	70	64	61	77	69	64	61		68	64	61			68	64	61			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1624598
5°	1607563
10°	1581095
15°	1439717
20°	1198006
25°	850401
30°	450126
35°	183428
40°	68120
45°	31182
50°	12782
55°	6686
60°	3278
65°	982
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31182 cd/sqm



TEST NUMBER: P756466

CATALOG NUMBER: LD4D95BD010-EU4DR5070959035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1385.4	15.0
10°-20°	3501.2	37.9
20°-30°	3145.0	34.1
30°-40°	984.7	10.7
40°-50°	172.4	1.9
50°-60°	34.4	0.4
60°-70°	5.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8031.6	87.0
0°-40°	9016.3	97.7
0°-60°	9223.0	99.9
0°-90°	9228.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9228.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14869	
5°	14657	###
15°	12728	3501
25°	7054	3145
35°	1375	985
45°	202	172
55°	35	34
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756466

CATALOG NUMBER: LD4D95BD010-EU4DR5070959035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	14869.0
2.5°	14795.0
5°	14657.1
7.5°	14446.5
10°	14251.0
12.5°	13624.2
15°	12727.9
17.5°	11589.6
20°	10303.4
22.5°	8815.4
25°	7054.0
27.5°	5186.2
30°	3567.8
32.5°	2322.9
35°	1375.2
37.5°	789.8
40°	477.6
42.5°	310.9
45°	201.8
47.5°	122.9
50°	75.2
52.5°	51.4
55°	35.1
57.5°	23.8
60°	15.0
62.5°	8.8
65°	3.8
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)