

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756622

Luminaire Tested: LD4D95BD010-EU4DR6070959035-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756622
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR6070959035-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8924.8 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756622

CATALOG NUMBER: LD4D95BD010-EU4DR6070959035-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P756622

CATALOG NUMBER: LD4D95BD010-EU4DR6070959035-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	975852
5°	973459
10°	1005795
15°	1006837
20°	926392
25°	787965
30°	600399
35°	424584
40°	249317
45°	100607
50°	33588
55°	16173
60°	6643
65°	982
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 100607 cd/sqm



TEST NUMBER: P756622

CATALOG NUMBER: LD4D95BD010-EU4DR6070959035-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	856.2	9.6
10°-20°	2465.9	27.6
20°-30°	2951.3	33.1
30°-40°	1974.0	22.1
40°-50°	585.3	6.6
50°-60°	84.2	0.9
60°-70°	8.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6273.4	70.3
0°-40°	8247.4	92.4
0°-60°	8916.8	99.9
0°-90°	8924.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8924.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8931	
5°	8876	856
15°	8901	2466
25°	6536	2951
35°	3183	1974
45°	651	585
55°	85	84
65°	4	8
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756622

CATALOG NUMBER: LD4D95BD010-EU4DR6070959035-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	8931.4
2.5°	8920.0
5°	8875.6
7.5°	8996.0
10°	9065.6
12.5°	9053.0
15°	8901.0
17.5°	8542.5
20°	7967.4
22.5°	7277.1
25°	6536.1
27.5°	5701.3
30°	4758.9
32.5°	3917.8
35°	3183.2
37.5°	2447.2
40°	1748.0
42.5°	1152.7
45°	651.1
47.5°	333.1
50°	197.6
52.5°	127.9
55°	84.9
57.5°	54.5
60°	30.4
62.5°	12.7
65°	3.8
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)