

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756201

Luminaire Tested: LD4D95BD010-EU4DR3570959027-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756201
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR3570959027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8570.2 lumens
Efficiency: N/A
Efficacy: 86.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756201

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P756201

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2576467
5°	2515928
10°	2267520
15°	1759957
20°	998226
25°	388359
30°	144886
35°	79416
40°	51903
45°	31599
50°	20109
55°	14211
60°	10402
65°	5662
70°	415
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31599 cd/sqm

TEST NUMBER: P756201

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2109.7	24.6
10°-20°	4119.1	48.1
20°-30°	1679.9	19.6
30°-40°	402.0	4.7
40°-50°	167.5	2.0
50°-60°	69.3	0.8
60°-70°	21.7	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7908.8	92.3
0°-40°	8310.8	97.0
0°-60°	8547.7	99.7
0°-90°	8570.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8570.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	23581	
5°	22939	###
15°	15559	4119
25°	3221	1680
35°	595	402
45°	204	168
55°	75	69
65°	22	22
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P756201

CATALOG NUMBER: LD4D95BD010-EU4DR3570959027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	23580.9
2.5°	23439.4
5°	22939.2
7.5°	21941.3
10°	20438.0
12.5°	18321.3
15°	15559.0
17.5°	12180.7
20°	8585.2
22.5°	5474.4
25°	3221.4
27.5°	1820.9
30°	1148.4
32.5°	806.3
35°	595.4
37.5°	460.4
40°	363.9
42.5°	280.3
45°	204.5
47.5°	153.0
50°	118.3
52.5°	93.9
55°	74.6
57.5°	60.4
60°	47.6
62.5°	34.7
65°	21.9
67.5°	7.7
70°	1.3
72.5°	1.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)