

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P756512

Luminaire Tested: LD4D95BD010-EU4DR5570959027-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P756512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D95BD010-EU4DR5570959027-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8738.1 lumens
Efficiency: N/A
Efficacy: 88.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P756512

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P756512

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1070581
5°	1028057
10°	1024189
15°	994768
20°	891952
25°	737151
30°	556822
35°	403736
40°	258388
45°	118005
50°	38602
55°	16649
60°	7168
65°	931
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 118005 cd/sqm



TEST NUMBER: P756512

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	891.9	10.2
10°-20°	2434.3	27.9
20°-30°	2774.1	31.7
30°-40°	1888.5	21.6
40°-50°	650.8	7.4
50°-60°	90.0	1.0
60°-70°	8.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6100.2	69.8
0°-40°	7988.7	91.4
0°-60°	8729.4	99.9
0°-90°	8738.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8738.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9798	
5°	9373	892
15°	8794	2434
25°	6115	2774
35°	3027	1888
45°	764	651
55°	87	90
65°	4	9
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P756512

CATALOG NUMBER: LD4D95BD010-EU4DR5570959027-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9798.4
2.5°	9573.8
5°	9373.4
7.5°	9275.1
10°	9231.4
12.5°	9085.7
15°	8794.3
17.5°	8331.7
20°	7671.2
22.5°	6908.7
25°	6114.6
27.5°	5287.7
30°	4413.5
32.5°	3672.9
35°	3026.9
37.5°	2412.6
40°	1811.6
42.5°	1255.5
45°	763.7
47.5°	411.6
50°	227.1
52.5°	134.8
55°	87.4
57.5°	55.9
60°	32.8
62.5°	14.6
65°	3.6
67.5°	1.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)